UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 17-4J14-Z

EVAPCO, INC. evapco



DWG. # REV. EG171408-DRC-SF DATE 11/4/2025 SERIAL #


NOTES:

1. (M)- FAN MOTOR LOCATION


2. HEAVIEST SECTION IS UPPER SECTION


3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END

- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS
- 8. 3/4" [18mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 10. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



FACE A





SHIPPING WEIGHT

32320 lbs+ [14665] kg+

OPERATING WEIGHT

46260 lbs+ [20985] kg+

HEAVIEST SECTION WEIGHT

14080 lbs+ [6390] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: **Drawn**