UNIT	COOLING TOWER		
MODEL #	AT 110-2M12	SCALE NTS	

EVAPCO, INC. Evapeo

WG. #	T3TM1224-DRD-ST	REV
ERIAL #		DATE 11/5/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]




FACE C


ACCESS DOOR

FACE D

FACE B PLAN VIEW

FACE A





SHIPPING 6890 lbs+ [3130] kg+ WEIGHT

OPERATING WEIGHT

11850 lbs+ [5380] kg+

HEAVIEST SECTION WEIGHT

4470 lbs+ [2030] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG