UNIT	COOLING TO	WER
MODEL #	AT 312-2J36	SCALE NTS

EVAPCO, INC. Evapeo

FACE B

PLAN VIEW


DWG. # T3123C24-DRF-ST REV. SERIAL # DATE 11/6/2025

FACE D


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] mm

FACE C



FACE A





SHIPPING WEIGHT 23040 lbs+ [10455] kg+ OPERATING WEIGHT 41670 lbs+ [18905] kg+ HEAVIEST SECTION WEIGHT 5000 lbs+ [2270] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: BLL