UNIT CLOSED CIRCUIT COOLER			<b>5</b> \/A	EVAPCO, INC. Evapeo			DWG. # WB3122012-DRC-SF		REV.
MODEL #	ATWB 12-6O20-Z	SCALE NTS	† EVA	PCO, II	VC.		SERIAL #		DATE 11/6/2025
2. HÉAVIE 3. MPT DE FPT DE BFW DI GVD DE FLG DE PE DEN 4. + UNIT ACCES FOR A 5. MAKE-L 20 psi N 6. * - APPI FOR PF PIPING 7. SERIES DRAIN 8. 3/4" [19	AN MOTOR LOCATION EST SECTION IS UPPER SE ENOTES MALE PIPE THREA ENOTES BEVELED FOR WE ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU SCORIES (SEE SEPARATE I CCESSORIES) JP WATER PRESSURE MIN [137 KPa], 50 psi MAX [3- ROXIMATE DIMENSIONS DE RE-FABRICATION OF CONN S FLOW PIPING AND AUX. O BY OTHERS MMJ DIA. MOUNTING HOLE MMENDED STEEL SUPPOR	AD EAD ELDING  DE DRAWINGS  44 kPa] O NOT USE DECTING  CROSSOVER ES. REFER TO		FACE B PLAN VIEW		<u>F4</u>	ACE C  ACCESS DOOR	FACI	<u>E D</u>
9. DIMENS	MMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	i drawing. S:	[ 7" [ 178] ]		1'-3 1/4" [ 387 ]	E#	ACE A		
	(4) 4" [100] BFW FLUID IN	5'-9 1/4" *	3'-3/8" *		(4) 1/2" [15] FPT VENT	JC=			
	3'-11 3/4" *		(4) 4" [100] BFW FLUID OUT	5 1/8"   SERIES FLOV (SEE NO   16'-7 3/8"   5064 ]		6			
	2" [50] MPT — MAKE-UP 2'-1 1/4" [ 643 ]		6" * 6'-2 [ 18 ] 1'-5" [ 433 ]	AUX. CROSSC (SEE NI 1/4" 84]	OVER DRAIN				
	3 5/8" DF	[80] MPT tAAIN  5 1/4" [ 133] 1/4" [08]	BO] MPT RFLOW						
		7'-2" 2184] —— [ 3607] —— [ FACE B			2'-1/2" [ 622 ]	- E#	- [20'-0"	_	
SHIPPING WEIGHT	34190 lbs+ [15	510] kg+	OPERATING 52760 I	lbs+ [23935] kg+	HEAVIEST SECTION WEIGHT	29680 lbs+ [13465] k	g+ NO. OF SHIPPING SECTION	NS 2	RAWN BY: JLG