UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 14-4J12-Z

EVAPCO, INC. Evapeo




REV. CW4C141208-DRA-SF

SERIAL #


DATE 11/5/2025


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



DWG. #





**SHIPPING** WEIGHT

34500 lbs+ [15650] kg+

**OPERATING** WEIGHT

40880 lbs+ [18545] kg+

HEAVIEST SECTION WEIGHT

13620 lbs+ [6180] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM