UNIT	CLOSED CIRCUIT COOLER		
MODEL #	eco-ATWB 12-6O20	SCALE NTS	

EVAPCO, INC. Evapca


DWG. # WB3122012-DRC-ST REV. SERIAL # DATE 11/6/2025


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

FACE B
PLAN VIEW

FACE A

FACE C





SHIPPING WEIGHT 43100 lbs+ [19550] kg+ OPERATING WEIGHT 61670 lbs+ [27975] kg+ HEAVIEST SECTION WEIGHT 38590 lbs+ [17505] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR