EVAPCO, INC. UNIT SERIAL # MODEL # SCALE **EVAPORATIVE CONDENSER** NTS C2122412-MRB-SLF 7/16/2025 eco-PMC-869 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES) 3607 5. 19mm DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT 6. MAKE-UP WATER PRESSURE-137 kPa MIN, FACE 1 344 kPa MAX 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING. 8. MAKE-UP IS LOCATED 121mm FROM EACH 7366 CONNECTION END. FACE 2 **PLAN VIEW −** 178 933 **ACCESS** ACCESS M DOOR 933 **─** 1740 **─** 3699 (4) 100 BFW REFRIG IN 5582 1213 (4) 100 BFW REFRIG OUT (2) 50 MPT -MAKE-UP 133 1883 638 432 (2) 80 MPT 89 (2) 80 MPT 1422 **OVERFLOW** 3607 467 -7366 -FACE 1 FACE 2 NO. OF SHIPPING SECTIONS SHIPPING OPERATING HEAVIEST SECTION 4 21135 27975 kg 9410 ka kg WEIGHT WEIGHT WEIGHT