UNIT	OL OOFD OIDOUT OO	OL ED	1		®	DWG. #	CT REV.
MODEL #	CLOSED CIRCUIT CO	CCALE	EVAPCO, I	NC. Evap	CO	WB3241412-DRC- SERIAL #	51 -
NOTES: 1. (M)-F. 2. HEAV 3. MPT [FPT D BFW I GVD [FLG D 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APP FOR F PIPIN 7. 3/4" [1 RECO	AN MOTOR LOCATION IEST SECTION IS UPPER SE DENOTES MALE PIPE THRE DENOTES FEMALE PIPE THRE DENOTES BEVELED FOR W DENOTES FLANGE ENOTES PLAIN END WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSORY -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 ROXIMATE DIMENSIONS DO PRE-FABRICATION OF CONN G 9mm] DIA. MOUNTING HOLE MMENDED STEEL SUPPOR NSIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	ECTION AD READ ELDING JDE Y DRAWINGS) A44 kPa] O NOT USE NECTING ES. REFER TO		PLA	FACE B N VIEW	FACE C (2) ACCESS DOOR	PACE D
	3'-11 3/4" * [1213] *	(2) 2" [50] MPT MAKE-UP (2) 3" [80] MF DRAI 5 1/8 [130	FLUID OUT 6" 11'-4 3/4" [34'8" 11'-5 3/4" [3499]	7" [178] 10'-5 1/8" [3180] 17'-7 3/8" [5369] 7'-2 1/4" [2189] - 1'-5" [433]	1'-3 1/4" [387] (4) 1/2" [15] FPT VENT 1'-6 1/2" [470]	13'-11 3/4" [4261]	
SHIPPING WEIGHT	61300 lbs+ [278	810] kg+	OPERATING 87240 lbs+ [39575] kg+	HEAVIEST SECTION 275	590 lbs+ [12515] kg+	NO. OF SHIPPING SECTIONS	4 DRAWN BY: SLR