

EVAPCO, INC.




UNIT	CLOSED CIRCUIT COOLER	MODEL #	ESWA-672-440	SCALE	NTS	DWG. #	WZ14484808DRC-ST	REV.		DATE	6/26/2025	SERIAL #	
------	-----------------------	---------	--------------	-------	-----	--------	------------------	------	--	------	-----------	----------	--

NOTES:


1. (M) - FAN MOTOR LOCATION
2. HEAVIEST SECTION IS LOWER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
6. MAKE-UP WATER PRESSURE
20 PSI [137 KPA] MIN,
50 PSI [344 KPA] MAX
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
8. MAKE-UP IS LOCATED 4 3/4" [121MM] FROM EACH CONNECTION END.

**FACE 2
PLAN VIEW**



MAKE-UP
DRAIN
OVERFLOW
(BOTH ENDS)

FACE 1



SHIPPING WEIGHT	72980 lbs. + [33105] kg. +	OPERATING WEIGHT	110664 lbs. [50195] kg.	HEAVIEST SECTION WEIGHT	22830 lbs. [10355] kg.	NO. OF SHIPPING SECTIONS	2
-----------------	----------------------------	------------------	-------------------------	-------------------------	------------------------	--------------------------	---