

NOTES:

- (M)- FAN MOTOR LOCATION
- HAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH IN
[METRIC] [mm]


7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

The technical drawing consists of two main views: FACE 2 PLAN VIEW and FACE 1 ELEVATION VIEW.

FACE 2 PLAN VIEW: This view shows the top-down layout of the unit. It features four fan motors (M) arranged in a square pattern. The overall dimensions are 24'-1 1/8" [7344] by 11'-11 3/4" [3651]. Key dimensions include a central spacing of 5 1/8" [130] between fans, a distance of 69 3/8" [1762] from the center to the edge, and a total width of 27 5/8" [702] for the fan assembly. Pipe connections are detailed with labels such as (4) 4 [100] BFW INLET, (4) 4 [100] BFW OUTLET, (2) 3 [80] MPT OVERFLOW, (2) 2 [50] MPT MAKE-UP, and (2) 3 [80] MPT DRAIN. Other dimensions shown include 56 1/4" [1427], 105 3/4" [2684], 36 3/8" [922], 74 1/8" [1883], 25 1/4" [641], 5 7/8" [149], 5 1/4" [133], 4 1/4" [108], 3 5/8" [92], and 17" [432].

FACE 1 ELEVATION VIEW: This view shows the front elevation of the unit. It includes two access doors at the top, crossover piping (by others), and a large coil section at the bottom. The overall height is 213 7/8" [5432]. The width is 11'-11 3/4" [3651]. A dimension of 7" [178] is shown for the top section, and 18 1/4" [464] for the base section.

SHIPPING WEIGHT	OPERATING WEIGHT	HAVIEST SECTION WEIGHT	NO. OF SHIPPING SECTIONS	DRAWN BY:
40040 lbs+ [18165] kg+	54000 lbs+ [24495] kg+	16430 lbs+ [7455] kg+	6	SFR



FACE 1