## EVAPCO, INC.



UNIT SERIAL # REV. N.T.S. ATC-DC-2414M-35-2EF EGCH241404-DRD-ST 8/21/2025 **EVAPORATIVE CONDENSER** NOTES: 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS COIL SECTION TO RECOMMENDED STEEL SUPPORT DRAWING. 3. MPT DENOTES MALE PIPE THREAD 7. \* - APPROXIMATE DIMENSIONS DO FPT DENOTES FEMALE PIPE THREAD NOT USE FOR PRE-FABRICATION BFW DENOTES BEVELED FOR WELDING OF CONNECTING PIPING. **GVD DENOTES GROOVED** FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 2 PLAN VIEW 5 1/8 <sub>-</sub> [ 130 ] FACE 1 7 [ 178 ] - (4) 4 [100] BFW INLET (M) (11) 6 7/8 **CROSSOVER ACCESS PIPING** 105 3/4 <sub>\*</sub> [ 2684 ] 33 1/2 [ 851 ] **DOORS** (BY OTHERS) 36 3/8 \* [ 922 ] 225 7/8 5 7/8 \* [ 149 ] (4) 4 [100] BFW 86 1/8 [ 2188 ] ÒÚTLĒT 25 1/4 [ 641 ] 3 5/8 [ 92 ] 5 1/4 [ 133 ] 17 [ 432 ] (2) 3 [80] MPT (2) 2 [50] MPT 4 1/4 [ 108 ] 18 1/4 [ 464 ] 56 [ 1422 ] MAKE-UP **OVERFLOW** (2) 3 [80] MPT 142 [ 3607 ] FACE 1 DRAIN FACE 2 OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** HEAVIEST SECTION SFR 21820 lbs+ [9900] kg+ 49360 lbs+ [22390] kg+ 66220 lbs+ [30040] kg+

WEIGHT

WEIGHT

WEIGHT