

NOTES: (M) - FAN MOTOR LOCATION - HEAVIEST SECTION IS COIL SECTION - MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) - MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]	- DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE 2 <u>PLAN VIEW</u> 
--	---	--



Technical drawing of the front view of a 36-inch wide, 2 1/2-inch high unit. The drawing shows a rectangular cabinet with two main sections. The left section has a top panel with a crossover piping connection and a bottom panel with two access doors. The right section has a top panel with a crossover piping connection and a bottom panel with two access doors. Dimensions are provided in inches and millimeters. The total width is 36 inches (914 mm). The total height is 2 1/2 inches (64 mm). The distance between the two main sections is 19 inches (484 mm). The distance from the left edge to the first section is 19 inches (484 mm). The distance from the second section to the right edge is 19 inches (484 mm). The distance between the two access doors in each section is 2 1/2 inches (64 mm). The drawing is labeled "FACE 1".



SHIPPING WEIGHT	62120 lbs+ [28180] kg+	OPERATING WEIGHT	83690 lbs+ [37965] kg+	HEAVIEST SECTION WEIGHT	27800 lbs+ [12610] kg+	NO. OF SHIPPING SECTIONS	6	DRAWN BY:	SFR
-----------------	------------------------	------------------	------------------------	-------------------------	------------------------	--------------------------	---	-----------	-----