

UNIT	CLOSED CIRCUIT COOLER		EVADOO TNO EVAPOO	DWG. # EG171208-DRC-SF	REV.
MODEL #	eco-ATWB 17-4J12-Z	SCALE NTS	EVAPCO, INC.	SERIAL #	DATE 11/5/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MEDITIONS MALE PIPE THEFAD				FACE C	


- 2. HEAVILED SECTION IS OF THE CHOICE
 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]



FACE D

FACE A





FACE A

NO. OF SHIPPING SECTIONS 4 DRAWN BY: JLG