| JNIT | CLOSED CIRCUIT COOLER | |
|---------|-----------------------|-----------|
| 10DEL # | eco-ATWB 17-4L12-Z | SCALE NTS |




DWG. # WB3171208-DRD-SF REV. SERIAL # DATE 11/4/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]


FACE C



FACE B

PLAN VIEW

FACE D



SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7) 1'-3 5/8" 1'-3 5/8" 11'-11 3/4" FACE A

12430 lbs+ [5640] kg+

SHIPPING 28600 lbs+ [12975] kg+

OPERATING WEIGHT

40600 lbs+ [18420] kg+

HEAVIEST SECTION WEIGHT NO. OF SHIPPING SECTIONS

DRAWN BY: JLG