NIT CONDENSER			EVAPCO, INC. Evapco			DWG. # WB3124010-DRC-ST	REV.
MODEL #	ATC-1625E	SCALE NTS	EVAP	CO, IN		SERIAL #	DATE <sub>12/12/2025</sub>
2. HÉAVIEST 3. MPT DENO FPT DENO BFW DENO GVD DENO FLG DENO PE DENOT 4. +UNIT WEI ACCESSOI 5. MAKE-UP \( 20 \) psi MIN 6. *-APPROXI FOR PRE-F PIPING 7. 3/4" [19mm RECOMME 8. DIMENSIOI	IOTOR LOCATION SECTION IS UPPER SE STES MALE PIPE THREA TES FEMALE PIPE THREA STES BEVELED FOR WI STES GROOVED TES FLANGE ES PLAIN END GHT DOES NOT INCLUI RIES (SEE ACCESSORY WATER PRESSURE [137 kPa], 50 psi MAX [3- MATE DIMENSIONS DO FABRICATION OF CONN I] DIA. MOUNTING HOLE INDED STEEL SUPPOR' NS LISTED AS FOLLOW NGLISH FT-IN IETRIC [mm]	AD IEAD ELDING  DE ( DRAWINGS)  44 kPa] D NOT USE IECTING ES. REFER TO T DRAWING.	<u>PLAN</u>	FACE B VIEW	ACCESS DOOR  FACE	ACCESS DOOR	FACE D
3'-3 3'-3 [ 99 (2) 2" [50] MAK 2'-1 1/4" [ 643] 1 3 5/8 [ 92	MPT - (4) 4" [100] PE E-UP - (2) 3" [80] MPT		9'-8 5/8" [ 2964] 16'-10 7/8" [ 5153] * 7'-2 1/4" [ 2189]	1'-3 1/4" [ 387 ]	20'-0" [6096]		2'-1/2" [ 622]