UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-6N12-Z	SCALE NTS

EVAPCO, INC. Evapco

DWG. # REV. WB3121212-DRC-SF DATE 11/6/2025 SERIAL #

NOTES:


- 1. (M) FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]



FACE C ACCESS DOOR FACE B FACE D PLAN VIEW

FACE A





SHIPPING 26680 lbs+ [12105] kg+ WEIGHT

OPERATING WEIGHT

37740 lbs+ [17120] kg+

HEAVIEST SECTION WEIGHT

23970 lbs+ [10875] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG