


UNIT		CONDENSER		<div>EVAPCO, INC.</div> <div></div>	DWG. #	WB34M1212-DRC-ST	REV.	-	
MODEL #		ATC-M685E	SCALE		NTS	SERIAL #		DATE	

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HEAVIEST SECTION IS UPPER SECTION

3. MPT DENOTES MALE PIPE THREAD

FPT DENOTES FEMALE PIPE THREAD

BEFW DENOTES BEVELED FOR WELDING

GVD DENOTES GROOVED

FLG DENOTES FLANGE

PE DENOTES PLAIN END

4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)

5. MAKE-UP WATER PRESSURE

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING

7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN

METRIC [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

FACE B

FACE A

1'-9 3/8" [543]

3'-9 1/4" [1149] *

2'-3 3/8" [619] *

8'-10" [2694]

13'-10 1/4" [4223]

3'-6" [1067] *

1'-11 1/8" [589]

3" [76]

2'-6 1/2" [775]

1'-3" [383]

7'-4 3/4" [2254]

7'-5 3/4" [2280]

7'-10" [2388]

5 1/8" [130]

16'-1 1/8" [4905]

6" [154] *

5'-1 1/4" [1529]

(4) 4" [100] PE REFRIG IN

(4) 4" [100] PE REFRIG OU

(2) 2" [50] MPT MAKE-UP

(2) 2" [50] MPT DRAIN

(2) 3" [80] MPT OVERFLOW

FACE B

1'-7/8" [327]

1'-4 5/8" [421]

11'-11 3/4" [3651]

FACE A

SHIPPING WEIGHT	28340 lbs+ [12855] kg+	OPERATING WEIGHT	35880 lbs+ [16275] kg+	HEAVIEST SECTION WEIGHT	12400 lbs+ [5625] kg+	NO. OF SHIPPING SECTIONS	4	DRAWN BY:	SLR
-----------------	------------------------	------------------	------------------------	-------------------------	-----------------------	--------------------------	---	-----------	-----