


UNIT <b>CLOSED CIRCUIT COOLER</b>		<b>EVAPCO, INC.</b> 	DWG. # WB3TM1210-DRC-ST	REV. -
MODEL # eco-ATWB 10-5K12	SCALE NTS		SERIAL #	DATE 6/22/2025


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]

**FACE B**


**PLAN VIEW**

**FACE C**




**FACE D**

**FACE B**



**FACE A**



SHIPPING WEIGHT	19850 lbs+ [9005] kg+	OPERATING WEIGHT	28680 lbs+ [13010] kg+
		HEAVIEST SECTION WEIGHT	17300 lbs+ [7850] kg+
		NO. OF SHIPPING SECTIONS	2
		DRAWN BY:	SLR