INIT	CONDENSER		_			0	D	wg. # CW4C141414-DRB-ST	REV -
10DEL#	ATC-821E	SCALE NT	S I	EVAPCO, I	INC.	/apco	S	ERIAL#	DATE: 11/3/2025
2. HEAVIES 3. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENC 4. +UNIT W ACCESS 5. MAKE-UF 20 psi MII 6. *-APPRO FOR PRE PIPING 7. 3/4" [19m RECOMM 8. DIMENSI	MOTOR LOCATION IT SECTION IS FAN/CA: IOTES MALE PIPE THR OTES FEMALE PIPE TH NOTES BEVELED FOR NOTES GROOVED OTES FLANGE DIES PLAIN END EIGHT DOES NOT INCL ORIES (SEE ACCESSO P WATER PRESSURE N [137 kPa], 50 psi MAX XIMATE DIMENSIONS I E-FABRICATION OF CO m] DIA. MOUNTING HO MENDED STEEL SUPPO ONS LISTED AS FOLLO ENGLISH FT-IN METRIC [mm]	READ HREAD WELDING LUDE HRY DRAWING [344 kPa] DO NOT USE NNECTING HLES. REFER DRT DRAWIN	GS)		FAC PLAN			FACE C (M) ACCESS DOOR SS DOOR (M)	FACE D
3'-11	3/4" [1213] (d) 4" [100] PE (d) 4" [100] PE (d) 4" [100] PE (d) 4" [100] PE (e) 4" [100] PE (f) 5 (6) -10 7, [2105 6'-11 3, [2127 7'-4' [2238]	REFRIGUT O (8") 1	(2) 2" [50] MPT MAKE-UP (2) 2" [50] MPT DRAIN 5 1/8" 130]	1'-10 7/8" [581] 2'-11 3/8" [899] (M) 6'-5 1/8" [1959] 14'-10 3/4" [49] 5 1/4" [133] 5'-6 1/4" [1683] 1'-3" [381] (2) 3" [80] MPT OVERFLOW	539]	1'-2" [3	355]	13'-11 3/4" [4261]	
FACE B								FACE A NO. OF SHIPPING SECTIONS	DRAWN BY:
SHIPPING WEIGHT 31220 lbs+ [14165] kg+		kg+	OPERATING WEIGHT	33370 lbs+ [15140] kg+	HEAVIEST SECTION WEIGHT	13420 lbs+ [6090)] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG