



UNIT COOLING TOWER		EVAPCO, INC. 	DWG. # T3041224-DRJ-ST	REV. -
MODEL # AT 14-2G12	SCALE NTS		SERIAL #	DATE 12/15/2025

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B




FACE B

FACE A



FACE A

FACE C



FACE D

SHIPPING WEIGHT 2570 lbs+ [1170] kg+	OPERATING WEIGHT 4690 lbs+ [2130] kg+	HEAVIEST SECTION WEIGHT 1810 lbs+ [825] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: KWC
---	--	--	-------------------------------	------------------