COOLING TOWER  NOTES: 1. MP-FAN MOTOR LOCATION  NOTES: 1. MP-FAN M	UNIT	COOLING TOW	ER	FV/ADCO	TNIC	evanco	DWG. # T4282660-DRA-ST		REV.
1. (M) FAN MOTOR LOCATION 2. PEACE TO NO SUPPRESCRICTION 3. PEACE TO NO SUPPRESCRICTION 4. FUNT WEIGHT DOES NOT INCLIDE 4. FUNT WEIGHT DOES NOT INCLIDE 4. PEACE TO NO SUPPRESCRICTION 3. PEACE TO NO SUPPRESCRICTION 4. PEACE TO NO SUPPRESCRICTION 5.	MODEL #	AT 228-5K26	SCALE NTS	EVAPCO	, INC.		SERIAL #		DATE 11/21/2025
12 14" [36] BFW/G/D BF	1. (M)- FA 2. HEAVIE 3. MPT DE FPT DE BFW D GVD DE FLG DE PE DEN 4. +UNIT 20 psi N 6. 3/4" [19 REFER DRAWI 7. DIMEN:	EST SECTION IS UPPER SENOTES MALE PIPE THRE SHOTES FEMALE PIPE THE ENOTES BEVELED FOR VENOTES GROOVED SHOTES PLAIN END WEIGHT DOES NOT INCLUSORIES (SEE ACCESSOF UP WATER PRESSURE WIN [137 kPa], 50 psi MAX [WMJ DIA. MOUNTING HOLITO RECOMMENDED STENG SIONS LISTED AS FOLLOW GLISH FT-IN	EAD READ VELDING  JDE RY DRAWINGS)  344 kPa] ES. EL SUPPORT					(4) ACCESS DOOR	FACE D
28'-3 5/8" 25'-9" 25'-9"	(2)	(2) 14" [350] — BFW/GVD OUTLET (2) 4" [100] MPT OVERFLOW (2) 3" [80] MPT MACK-UI (2) 4" [100] M DR/	MPT     - 13-5 410   - 13'-6 AIN   - 1412	6'-11 5/8" [2124]  16'-3 3 [4972]  16'-3 3 [4972]  1-5 3/8" [660] 1'-5 3/8" [441] 1/2" 9" [229] 81]		12'-1/4" [ 3664 ] 2" [ 51 ]			
FACE A		-	28'-3 5/8"	-		1 1/2" [ 38 ]			