
| UNIT | COOLING TOWER | |
|---------|---------------|-----------|
| MODEL # | AT 217-4J14 | SCALE NTS |


EVAPCO, INC. Evapeo


DWG. # T3171448-DRG-ST REV. SERIAL # DATE_11/22/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]







SHIPPING WEIGHT 13580 lbs+ [6160] kg+ OPERATING WEIGHT 22600 lbs+ [10255] kg+ HEAVIEST SECTION WEIGHT 4650 lbs+ [2110] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: KDS