
JNIT	CLOSED CIRCUIT COOLER	
10DEL #	ATWB 14-6K12-Z	SCALE NTS
NOTES:		




DWG. # REV. CW4C141212-DRA-SF DATE 11/4/2025 SERIAL #


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING **PIPING**
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

WEIGHT





WEIGHT



11630 lbs+ [5280] kg+

WEIGHT

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM