UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 14-3H18-Z

EVAPCO, INC. Evapeo





DWG. # REV. CW4C141806-DRA-SF DATE 11/5/2025 SERIAL #

NOTES:


WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





WEIGHT



17380 lbs+ [7885] kg+

WEIGHT

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM