UNIT	COOLING TO	ING TOWER	
MODEL #	AT 112-3I14	SCALE NTS	

EVAPCO, INC. Evapeo




DWG. # REV. T3121436-DRE-ST DATE 11/1/2025 SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]


FACE C


FACE B PLAN VIEW



FACE D

FACE A





DRAWN BY: KDS NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 8890 lbs+ [4035] kg+ 6020 lbs+ [2735] kg+ 16220 lbs+ [7360] kg+ WEIGHT WEIGHT WEIGHT