UNIT	COOLING TO	OWER
MODEL #	AT 19-3I8	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # T3090836-DRD-ST REV. SERIAL # DATE 11/6/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]





FACE B



FACE D

FACE A





OPERATING WEIGHT

6270 lbs+ [2845] kg+

HEAVIEST SECTION WEIGHT

2580 lbs+ [1175] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG