UNIT	COOLING TOWER	
MODEL #	AT 19-4G11	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # T3091148-DRD-ST REV.
SERIAL # DATE 11/18/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MÖUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]





FACE B



FACE D

FACE A





SHIPPING WEIGHT 5330 lbs+ [2420] kg+ OPERATING WEIGHT 8630 lbs+ [3915] kg+ HEAVIEST SECTION WEIGHT 3730 lbs+ [1695] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG