UNIT	COOLING TOWER	
MODEL #	AT 310-2M36	SCALE NTS
NOTES:	N MOTOR I OCATION	

EVAPCO, INC. Evapeo


FACE B


PLAN VIEW


DWG. # T3TM3C24-DRD-ST REV.
SERIAL # DATE 11/5/2025

- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]











FACE D

FACE A





OPERATING WEIGHT

36590 lbs+ [16600] kg+

HEAVIEST SECTION WEIGHT

4470 lbs+ [2030] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG