UNIT	COOLING TOWER	
MODEL #	AT 312-2N60	SCALE NTS





OWG. #	T3126024-DRD-ST	REV
SERIAL #		DATE 11/6/2025

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19MM] DIA. MOUNTING HOLES.
- 6. 3/4" [19MM] DIA. MOUNTING HOLES.
 REFER TO RECOMMENDED STEEL SUPPORT PLAN VIEW
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]

FACE B





FACE C



FACE D

FACE A

