UNIT	COOLING TOWER	
MODEL #	AT 19-4I14	SCALE NTS

EVAPCO, INC. Evapeo


DWG. # T3091448-DRD-ST REV. SERIAL # DATE 11/6/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN


[METRIC] [mm]


FACE B
PLAN VIEW



FACE D

FACE A





SHIPPING WEIGHT 6620 lbs+ [3005] kg+ OPERATING WEIGHT

11130 lbs+ [5050] kg+

HEAVIEST SECTION WEIGHT

4570 lbs+ [2075] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG