INIT COOLING TOWER			EVAPCO, INC. EVAPCO			DWG. #	T3124048-DRB-ST	REV.
IODEL #	AT 212-4K40	SCALE NTS	EVAPC	J, INC.		SERIAL #	:	DATE 11/21/2025
2. HEAVIES B. MPT DEI FPT DEN BFW DE GVD DE FLG DEN I. +UNIT W ACCESS 5. MAKE-U 20 psi MI 6. 3/4" [19M 7. DIMENS EN	N MOTOR LOCATION ST SECTION IS UPPER SE NOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES GROOVED NOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLUIT SORIES (SEE ACCESSORY P WATER PRESSURE IN [137 kPa], 50 psi MAX [3 MM] DIA. MOUNTING HOLI ENDED STEEL SUPPORT SIONS LISTED AS FOLLOV IGLISH FT-IN ETRIC] [mm]	AD EAD ELDING DE ' DRAWINGS) 44 kPa] ES. REFER TO DRAWING.	FACE B PLAN VIEW		ACCESS DOOR	CE C	ACCESS DOOR	FACE D
					FAC	CE A		
		7" [178]	1'-3 1/4" [387]					
			<u>. </u>					T I
	-	2" [51]	T	[10'-0"	- M		(M)	
		10'-4"] [3150]	 		0		(2) 10" [250] BFW/GVD	
		17'-6 [53	5 1/4" 340]				BFW/GVD INLET	
			 12'-1" [3683]					
		7'-2 1/4" [2191]						
			\ \\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\					
			2'-1 1/4" _	[3048]		(2) 3" [80] FPT OVERFLOW (2) 3" [80] FPT	(2) 10" [250] BFW/GVD OUTLET	
			1'-4 7/8" [429] 8 1/2" [216]		9'-3" 867] -6 3/4" 5963]	DRAIN (2) 2" [50] MPT MAKE-UP		
	111 1011	2/01	3 5/8" [92]		20'-0" 6096 1	2 1/2"		
11'-10" 3/8" [9] FACE B			40'-2 1/2" [12256] FACE A					
	IACLD				<u>FA</u>	ICE A		
SHIPPING WEIGHT	26200 lbs+ [11	885] kg+	OPERATING 47000 lbs+ [2132	20] kg+ HEAVIEST		010] kg+	OF SHIPPING SECTIONS 4	DRAWN BY: BLL