UNIT COOLING TOWER			EVADOO TI	NC evapeo °	DWG. # T3BI562660-DRD-ST	REV.
10del #	AT 456-5M26	SCALE NTS	EVAPCO, I	NC.	SERIAL #	DATE 11/5/2025
2. HÉAVIE: 3. MPT DE FPT DEI BFW DE GVD DE FLG DEI 4. +UNIT W ACCESS 5. MAKE-U 20 psi M 6. PAN EQ OTHERS 7. FOR BO SEE DE: 8. 3/4" [19r RECOMI 9. DIMENS ENG	I MOTOR LOCATION ST SECTION IS UPPER SEC NOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES BEVELED FOR WE NOTES GROOVED NOTES FLANGE VEIGHT DOES NOT INCLUE SORIES (SEE ACCESSORY P WATER PRESSURE IN [137 kPa], 50 psi MAX [34 UALIZER PIPING IS SUPPL S, FLUME SUPPLIED BY EV TTOM CONNECTION SPEC TAIL. nm] DIA. MOUNTING HOLE: MENDED STEEL SUPPORT IONS LISTED AS FOLLOWS GLISH FT-IN ETRIC] [mm]	DEAD LDING DE DRAWINGS) 4 kPa] IIED BY APCO. SIFICATIONS, DRAWING S: 2 1/8" 1 2 1/8" 1 7 1/8"	INSIDE BASIN 6'-11.5/ [2124	(2) ACCESS DOOR (2) ACCES 14" [350] 10 OUTLET 111'-3 1/2" [3442] 8" 16'-4 5/8" [4994] 21'-4" [6502]	FACE C ESS DOOR (2) ACCESS DOOR (2) ACCESS DOOR 11'-11'	FACE D 6'-11 5/8" [2124]
	25'-8 7/8" [7846] FACE B	10	7" [178] 2'-1/8" 3661] 22'-3 1/2" [6794] 1'-5 3/8" [441] 4" [102]	13'-61/2" — (4) 4" [1(OVERFICE — (4) 4" [1(57'-3/8"	
SHIPPING WEIGHT	99200 lbs+ [4500	0] kg+	DPERATING 166520 lbs+ [75535] kg+	HEAVIEST SECTION 17820 lbs+ [8085] kg	g+ NO. OF SHIPPING SECTIONS 8	DRAWN BY: SLR