UNIT	COOLING TOWER				avence.	DWG. # CT4C141224-DRA-ST	REV
MODEL #	AT 214-2K12	SCALE NTS	EVAPCO, 3	INC. E		SERIAL #	DATE _{11/21/2025}
2. HEAVII 3. MPT D FPT DE BFW D GVD D FLG DE 4. +UNIT ACCES 5. 3/4" [19 REFER SUPPO 6. DIMEN ENC [ME 7. MAKE-	AN MOTOR LOCATION EST SECTION IS FAN/CASII ENOTES MALE PIPE THRE ENOTES FEMALE PIPE THRE DENOTES BEVELED FOR WI DENOTES GROOVED ENOTES FLANGE WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSORY MM] DIA. MOUNTING HOLE R TO RECOMMENDED STEE DRT DRAWING ISIONS LISTED AS FOLLOW GLISH FT-IN ETRIC] [mm] -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3	AD READ ELDING DE ORAWINGS) ES. EL		2	FACE B PLAN VIEW	EACE C (2) ACCESS DOOR (2) FACE A	FACE D
		DJ MPT	3'-8" [1118] 8'-3 3/4" [2532] 1'-11 1/8" [587] 1'-2 7/8" [190] 7 1/2" [190] 3 5/8" [191]	12'-4 3/4" [3778]	2'-11 3/8" [899] 4'-5 1/8" [1349] [51] 5'-1/4" [1530]		
	-	15'-1 1/8" _ [4601] FACE B	-		1 3/8" [35]	11'-11 3/4" [3651] FACE A	

HEAVIEST SECTION WEIGHT

3230 lbs+ [1470] kg+

SHIPPING WEIGHT OPERATING WEIGHT

14930 lbs+ [6775] kg+

9960 lbs+ [4520] kg+

DRAWN BY:

NO. OF SHIPPING SECTIONS