



# EVAPCO, INC.




|               |             |        |                 |      |           |          |
|---------------|-------------|--------|-----------------|------|-----------|----------|
| UNIT          | MODEL #     | SCALE  | DWG. #          | REV. | DATE      | SERIAL # |
| COOLING TOWER | AT 310-2L54 | N.T.S. | T3TM5424-DRC-ST | -    | 11/4/2025 |          |

- NOTES:
1. (M)- FAN MOTOR LOCATION
  2. HEAVIEST SECTION IS UPPER SECTION
  3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING
  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
  5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

**FACE 2  
PLAN VIEW**



**FACE 2**



**FACE 1**

|                 |                        |                  |                        |                         |                      |                          |   |
|-----------------|------------------------|------------------|------------------------|-------------------------|----------------------|--------------------------|---|
| SHIPPING WEIGHT | 27720 lbs+ [12574] kg+ | OPERATING WEIGHT | 52940 lbs+ [24013] kg+ | HEAVIEST SECTION WEIGHT | 5910 lbs+ [2681] kg+ | NO. OF SHIPPING SECTIONS | 6 |
|-----------------|------------------------|------------------|------------------------|-------------------------|----------------------|--------------------------|---|