UNIT	COOLING TOWER	
MODEL #	AT 110-2J12	SCALE NTS


EVAPCO, INC. EVAPCO

DWG. # T3TM1224-DRD-ST REV. SERIAL # DATE 11/6/2025

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]







**FACE D** 

FACE B
PLAN VIEW

**FACE A** 





SHIPPING WEIGHT 6690 lbs+ [3035] kg+ OPERATING WEIGHT

11650 lbs+ [5285] kg+

HEAVIEST SECTION WEIGHT

4270 lbs+ [1940] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG