UNIT CLOSED CIRCUIT COOLER		COOLER
MODEL #	ATWB 4-4G12	SCALE NTS



DWG. # REV. WB3041208-DRE-ST DATE 11/4/2025 SERIAL #

FACE D

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN METRIC [mm]





FACE C

PLAN VIEW



FACE A





DRAWN BY: CAF NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 4890 lbs+ [2220] kg+ 5710 lbs+ [2595] kg+ 8870 lbs+ [4025] kg+ WEIGHT WEIGHT WEIGHT