UNIT	COOLING TOWER	
MODEL #	AT 19-4H9	SCALE NTS

EVAPCO, INC. Evapeo


DWG. # T3090948-DRD-ST REV. 
SERIAL # DATE 11/4/2025

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]


## FACE C


## FACE B



**FACE D** 

**FACE A** 





SHIPPING WEIGHT

4730 lbs+ [2150] kg+

OPERATING WEIGHT

7570 lbs+ [3435] kg+

HEAVIEST SECTION WEIGHT

3290 lbs+ [1495] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG