UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 9-6M12

EVAPCO, INC. Evapeo





DWG. # REV. WB3091212-DRC-ST SERIAL # DATE_{11/25/2025}


DRAWN BY: SLR

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 13210 lbs+ [5995] kg+ 15010 lbs+ [6810] kg+ 22130 lbs+ [10040] kg+ WEIGHT WEIGHT WEIGHT