

EVAPCO, INC.




UNIT	EVAPORATIVE CONDENSER	MODEL #	eco-PMC-1127	SCALE	NTS	DWG. #	C2241212-ERB-SLF	REV.		DATE	7/15/2025	SERIAL #	
------	-----------------------	---------	--------------	-------	-----	--------	------------------	------	--	------	-----------	----------	--

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
5. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE-20 psi MIN, 50 psi MAX
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.


FACE 1

24'-1 1/8"




FACE 2
PLAN VIEW

11'-11 3/4"



FACE 1



FACE 2

SHIPPING WEIGHT	46580	lbs. +	OPERATING WEIGHT	61660	lbs.	HEAVIEST SECTION WEIGHT	20750	lbs.	NO. OF SHIPPING SECTIONS	4
-----------------	-------	--------	------------------	-------	------	-------------------------	-------	------	--------------------------	---