


|         |                       |           |   |          |                  |                |
|---------|-----------------------|-----------|---|----------|------------------|----------------|
| UNIT    | CLOSED CIRCUIT COOLER |           | <b>EVAPCO, INC.</b>  | DWG. #   | WB3091412-DRC-ST | REV.           |
| MODEL # | ATWB 9-6L14           | SCALE NTS |   | SERIAL # |                  | DATE 1/12/2026 |


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. \*APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN  
METRIC [mm]



## FACE B



## FACE A

SHIPPING WEIGHT 17020 lbs+ [7725] kg+ OPERATING WEIGHT 25300 lbs+ [11480] kg+ HEAVIEST SECTION WEIGHT 15010 lbs+ [6810] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR