


EVAPCO, INC.




UNIT	MODEL #	SCALE	DWG. #	REV.	DATE	SERIAL #
EVAPORATIVE CONDENSER	eco-PMC-1336	N.T.S.	ECE122410-DRA-ST	-	6/20/2025	

- NOTES:
1. (M) - FAN MOTOR LOCATION
 2. HEAVIEST SECTION IS UPPER SECTION
 3. MPT DENOTES MALE PIPE THREAD
 - FPT DENOTES FEMALE PIPE THREAD
 - BFW DENOTES BEVELED FOR WELDING
 4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
 5. 3/4" DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
 6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
 7. * - APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN
[METRIC] [mm]

FACE 1
PLAN VIEW



FACE 1



FACE 2

SHIPPING
WEIGHT

49330 lbs+ [22376] kg+

OPERATING
WEIGHT

60090 lbs+ [27256] kg+

HEAVIEST SECTION
WEIGHT

19180 lbs+ [8700] kg+

NO. OF SHIPPING SECTIONS

3