| UNIT | CLOSED CIRCUIT COOLER | | EVAPCO, INC. Evapeo | | | DWG. # WB3122006-DR | C-ST REV |
|---|--|---|--|----------------------|------------|---------------------|----------------------------|
| MODEL # | ATWB 12-3O20 | SCALE NTS | EVAPCO |), INC. | | SERIAL # | DATE _{11/21/2025} |
| 2. HÉAVIE 3. MPT DI FPT DE BFW D GVD D FLG DE PE DEI 4. +UNIT 5. MAKE- 20 psi N 6. *-APPE FOR PI PIPING 7. 3/4" [18 RECON | IN MOTOR LOCATION EST SECTION IS UPPER S ENOTES MALE PIPE THRE ENOTES FEMALE PIPE THI ENOTES BEVELED FOR W ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUSORIES (SEE ACCESSOR UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [IN [137 kPa], 50 psi MAX [IN [147 kPa], | EAD READ READ VELDING JDE RY DRAWINGS) 344 kPa] O NOT USE NECTING RT DRAWING. | | FACE B | | FACE C ACCESS DOOR | FACE D |
| | METRIC [mm] | | | | | FACE A | |
| | | | 7" [178] | 1'-3 1 [387 | /4" 7] | | |
| | JCI | | | | | | r |
| | | 5'-9 1/4" * | 3'-3/8" * [924] * | (2) 1/2" FPT VE | [15] NT | (^) | |
| | 1'-10 1/4" * (2) 4" [[565] (2) 4" [100] | DO O O O O O O O O O O O O O O O O O O | 8'-3 5/8" [2532] 14'-5 7/8 [4416] | | | | |
| | 2" [50] MPT — MAKE-UP 2'-1 1/4" [643] | | 6" * 6'-2 1/4" [1884] 1'-5" [433] | | | | |
| | 3 5/8" 3" [8 DRA: | O V E I d E I | 1PT DW | | | | |
| | 4 1 [10 | | | | | | |
| | - | 11'-10" [3607] | | 2'-1/2" [622] → | | 20'-0" [6096] | _ |

HEAVIEST SECTION WEIGHT

18070 lbs+ [8200] kg+

SHIPPING WEIGHT OPERATING WEIGHT

22580 lbs+ [10245] kg+

37050 lbs+ [16810] kg+

DRAWN BY:

NO. OF SHIPPING SECTIONS