

MODEL #	X DIM	
	FT-IN	[mm]
ESWA 144-23I, 23J, 23K	4'-5 7/8 "	1368
ESWA 144-24I, 24J, 24K	4'-8 1/4 "	1429
ESWA 144-25I, 25J, 25K	4'-9"	1448
ESWA 144-26I, 26J, 26K	5'- 1/8 "	1527
ESWA 144-33I, 33J, 33K, 33L	4'-9"	1448
ESWA 144-34I, 34J, 34K, 34L	4'-11 1/4 "	1505
ESWA 144-35I, 35J, 35K, 35L	5'- 1/8 "	1527
ESWA 144-36I, 36J, 36K, 36L	5'-3 1/4 "	1607
ESWA 144-43J, 43K, 43L	5'- 1/8 "	1527
ESWA 144-44J, 44K, 44L, 44M	5'-2 3/8 "	1584
ESWA 144-45J, 45K, 45L, 45M	5'-3 1/4 "	1607
ESWA 144-46J, 46K, 46L, 46M	5'-6 1/4 "	1683

