EVAPCO, INC.

UNIT MODEL # REV. SERIAL # EGCH171204-DRC-ST N.T.S. **EVAPORATIVE CONDENSER** ATC-DC-1712K-25-2EF 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: (11) **ENGLISH IN** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 2
PLAN VIEW 17'-4 1/8" [5286] 48 5/8 * [1233] 5 1/8 [130] FACE 1 17 3/4 * [452] 52 7/8 (4) 4 [100] BFW ^[1341] 5 1/2 INLET [140] **CROSSOVER ACCESS PIPING** 33 1/2 * [851] **DOORS** (BY OTHERS) 75 [1906] 36 343/100 [0] [4987] [0] IJ 26 1/2 * [672] 0 5 7/8 [149] (4) 4 [100] BFW 60 1/8 [1527] OUTLET 23 1/8 [587] 5 1/4 [133] 3 [76] 15 [381] (2) 3 [80] MPT (2) 2 [50] MPT 4 1/4 34 [864] 18 1/4 11'-11 3/4" **OVERFLOW** MAKE-UP 108] [464] 3651 (2) 2 [50] MPT 101 1/2 [2578] FACE 1 DRAIN FACE 2 SHIPPING OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS DRAWN BY: SFR 28410 lbs+ [12890] kg+ 37020 lbs+ [16795] kg+ 11250 lbs+ [5105] kg+ WEIGHT WEIGHT WEIGHT