UNIT	CONDENSER		EVAPCO, INC. Evapeo		DWG. # WB3	3122010-DRC-ST	REV.	
MODEL #	ATC-869E	SCALE NTS	EVAPC	O, INC.	Evasco	SERIAL #		DATE 11/1/2025
2. HÉAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE PE DEN 4. +UNIT' ACCES 5. MAKE- 20 psi N 6. *-APPR FOR PI PIPING 7. 3/4" [19 RECON	N MOTOR LOCATION EST SECTION IS UPPER SE ENOTES MALE PIPE THRE, ENOTES FEMALE PIPE THRE ENOTES BEVELED FOR W ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU SORIES (SEE ACCESSOR' UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 OXIMATE DIMENSIONS DO RE-FABRICATION OF CONF mm] DIA. MOUNTING HOLE MENDED STEEL SUPPOR BIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	AD READ ELDING DE Y DRAWINGS) WHAT READ NOT USE NECTING ES. REFER TO T DRAWING.		FACE B PLAN VIEW		FACE C ACCESS DOOR FACE A	FACE	<u>D</u>
	JCI	5'-9 1/4" *	3'-3/8" * [924] *	1'-3 1/4' [387]	j. <u>jc</u>			
	3'-3 1/4" * [997] * (2) 4" [10] 2" [50] MPT MAKE-UP 2'-1 1/4" [643] 3 5/8" 3" [8 DRA 1 92] - 5	3" [80] MPT IN OVERFI	15'-10 7 [4848] 15'-10 7 [4848] 6'-2 1/4" [1884] 1'-5" [433]	7/8"				
	-	11'-10" [3607] FACE B		2'-1/2" [622]—				

HEAVIEST SECTION WEIGHT

25520 lbs+ [11580] kg+

SHIPPING WEIGHT OPERATING WEIGHT

41820 lbs+ [18970] kg+

30030 lbs+ [13625] kg+

DRAWN BY:

NO. OF SHIPPING SECTIONS