LINIT								100	DW	IC #		DEV/
UNIT	CONDENSER		_	EVAPCO, INC. Evapeo						DWG. # WB3122012-DRC-ST		REV.
MODEL #	ATC-967E	SCALE NTS		LVAPCO	<i>),</i> 11	10.			SEI	RIAL #		DATE _{10/29/2025}
2. HEAVIE 3. MPT DI FPT DE BFW D GVD D FLG DE PE DEI 4. +UNIT 4. +UNIT 20 psi N 6. *APPF FOR PI PIPING 7. 3/4" [15 RECOM	AN MOTOR LOCATION EST SECTION IS UPPER SE ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUE ESORIES (SEE ACCESSORY UP WATER PRESSURE WIN [137 kPa], 50 psi MAX [34 ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONN EMMENDED STEEL SUPPORT SIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	D EAD ELDING DE DRAWINGS) 14 kPa] NOT USE ECTING S. REFER TO DRAWING.			<u>PLAN</u>	FACE B VIEW			FACE O	ACCESS DOOR	FACE D	
	3'-11'3/4" * [1213] * (2) 4" [100] 2" [50] MPT — MAKE-UP 2'-1 1/4" [643]		RIG OUT	7" [178] '-3/8" * 924] * 10'-5 1/8" [3180] 16'-7 3/8" [5064] 6'-2 1/4" [1884] 1'-5" 433]		1'-3 1/4" [387]			20'-0" [6096]			
SHIPPING WEIGHT	34390 lbs+ [156	00] kg+	OPERATING WEIGHT	46490 lbs+ [21090] k	g+	HEAVIEST SECTION	ON	29880 lbs+ [13555] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY: SLR