NIT CONDENSER	EVARCO T	evança	DWG. # WB3122812-DRC-ST	REV
ATC-1204E SCALE NTS	EVAPCO, I	NC. Grand	SERIAL #	DATE _{12/11/2025}
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	FACE PLAN VIEV	-	ACCESS DOOR	FACE D
1 	[178] 1'-3 1) [387	4"		
5'-9 1/4" *	- 3'-3/8" *		(M)	
(2) 2" [50] MPT MAKE-UP (643] (2) 3" [80] MPT	6" * [154] * 7'-2 1/4" [2189]			
3 5/8"	1'-5" [433] —(2) 3" [80] MPT OVERFLOW 1'-4 3/ [425]	13'-11 3/4" [4261] 28'-2" [8585]		- 1'-4 3/4" [425]
### FACE B SHIPPING	OPERATING 65640 lbs+ [29775] kg+	HEAVIEST SECTION 21330 lbs+ [9680] kg+		DRAWN BY: SLR