UNIT	CLOSED CIRCUIT CO	DOLER	EVAPCO, II	NC eva	pco	DWG. # WB3241412-DR		
MODEL #	ATWB 24-6L14	SCALE NTS	EVAPCO, II	AC.	<u> </u>	SERIAL #	DATE 11/8/2025	
2. HEAVI 3. MPT D FPT DI BFW C GVD D FLG DI PE DE 4. +UNIT ACCES 5. MAKE- 20 psi I 6. *-APPF FOR P PIPING 7. 3/4" [18 RECOI	AN MOTOR LOCATION JEST SECTION IS UPPER SI JENOTES MALE PIPE THRE ENOTES BEVELED FOR WE JENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUS SORIES (SEE ACCESSOR JUP WATER PRESSURE MIN [137 kPa], 50 psi MAX [37 kPa], 50 psi MAX [47 kPa] ROXIMATE DIMENSIONS DO JEST SARRICATION OF CON GRE-FABRICATION OF CO	AD READ /ELDING JDE Y DRAWINGS) 344 kPa] O NOT USE NECTING ES. REFER TO RT DRAWING.		<u>PL</u>	FACE B AN VIEW	FACE C (2) ACCESS DOOR FACE A	FACE D	
	3'-11 3/4" *	(2) 2" [50] MPT MAKE-UP DRAII 5 1/8 [130	T (4) 4"[100] BFW FLUID OUT 6"	10'-5 1/8" [3180] 17'-7 3/8" [5369] 7'-2 1/4" [2189] - 1'-5" [433]	1'-3 1/4" [387] (4) 1/2" [15] FPT VENT 1'-6 1/2" [470]	13'-11 3/4" [4261]		
	FACE B							
SHIPPING WEIGHT	48780 lbs+ [22	130] kg+	OPERATING 74720 lbs+ [33895] kg+	HEAVIEST SECTION WEIGHT	21330 lbs+ [9680] kg+	NO. OF SHIPPING SECTIONS	4 DRAWN BY: SLR	