UNIT CONDENSER			<b>EV4 DGG</b>	TNIC	(avelage)	DWG. # CW4C071810-DRA-ST	REV.
MODEL #	ATC-407E	SCALE NTS	EVAPCO	, INC.	Evalue	SERIAL #	DATE 11/4/2025
2. HEAVIES 3. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENO 4. +UNIT WE ACCESSO 5. MAKE-UP 20 psi MIN 6. *-APPRO FOR PRE PIPING 7. 3/4" [19mi RECOMM 8. DIMENSIO	MOTOR LOCATION I SECTION IS FAN/CASII OTES MALE PIPE THRE/ DTES FEMALE PIPE THRE OTES BEVELED FOR W OTES GROOVED DTES FLANGE TES PLAIN END EIGHT DOES NOT INCLU DRIES (SEE ACCESSOR) WATER PRESSURE I [137 kPa], 50 psi MAX [3 KIMATE DIMENSIONS DO FABRICATION OF CONN m] DIA. MOUNTING HOLE ENDED STEEL SUPPOR DNS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	AD IEAD ELDING  DE ( DRAWINGS)  44 kPa] 0 NOT USE IECTING ES. REFER TO T DRAWING.	PLA	FACE B	ACCESS DO	FACE A	FACE D
2" [50] MP MAKE-U 2" [50] MP DRAI 1'-11 1, [ 587	P S S S S S S S S S S S S S S S S S S S	REFRIG OUT	2'-11 3/8" [ 899 ] - 1'-10 7/8" * [ 5'-3 7/8" [ 1622 ]   13'-3 1/2" [ 4051 ] - 5'-1/4" [ 1530 ] - 1'-3" [ 381 ] - 3" [80] MPT OVERFLOW	1'-2" [ 356 ]	-	18'-0" [5486]	
SHIPPING WEIGHT	18180 lbs+ [82	50] kg+	OPERATING	HEAVIEST SEC WEIGHT	TION 15160 lbs+ [6880] kg+	NO. OF SHIPPING SECTIONS 2	RAWN BY: TAM