UNIT CONDENSER						● D	owg. # CW4C072410-DRA-ST	REV.
10DEL # ATC-		SCALE NTS	⊣ E \	APCO, II	VC. evapeo	SE	ERIAL #	DATE 11/5/2025
BFW DENOTES BE GVD DENOTES GE FLG DENOTES PLA PE DENOTES PLA 4. +UNIT WEIGHT DO ACCESSORIES (S 5. MAKE-UP WATER 20 psi MIN [137 kP. 6. *-APPROXIMATE DE FOR PRE-FABRICA PIPING 7. 3/4" [19mm] DIA. M	ON IS FAN/CASING ALE PIPE THREAD MALE PIPE THREAD MALE PIPE THREAD EVELED FOR WELD ROOVED ANGE IN END DES NOT INCLUDE EE ACCESSORY DE PRESSURE a], 50 psi MAX [344 I) MENSIONS DO NO ATION OF CONNEC OUNTING HOLES. BETEEL SUPPORT DE ED AS FOLLOWS: I FT-IN	D DING RAWINGS) kPa] DT USE ETING REFER TO		FACE B PLAN VIEW	ACCESS D	FACE C	ACCESS DOOR TO THE PROPERTY OF THE PROPERTY O	FACE D
1'-9 3/8" [543] 2'-10 1/2" * [876] (2) 2" [50] MPT — MAKE-UP (2) 2" [50] MPT — DRAIN 1'-11 1/8" [587] 1'-76]	(4) 4" [100] PE RE (4) 4" [100] PE REF	FRIG OUT 1'-3 1 381	5'-1/4" [1530] " 1] " 2) 3" [80] MPT DVERFLOW	1'-5 1/8" [435]	11'-11 3/4" [3651]		2 1/2" [64]	1'-5 1/8" [435]
SHIPPING WEIGHT	33060 lbs+ [15000]	kg+	OPERATING WEIGHT 3	5900 lbs+ [16285] kg+	HEAVIEST SECTION 12900 lbs-	+ [5855] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: TAM